



Installation Tightening Guide Table

Number of Turns	Gland Size (mm)													Cable Diameter
	16MS1	16MS2	20MS1	20MS2	20MS3	20MS4	25MS1	25MS2	25MS3	25MS4	25MS5	25MS6	25MS7	
2.50						3.50								
3.00			5.00	4.00	4.00		6.00		8.00	6.00	7.00	5.00	6.00	
3.50	4.00	2.00			2.00			7.00			5.00	3.00	4.00	
4.00		1.00						5.00						
4.50														
5.00							3.00		5.00					
5.50	2.00					2.50					3.00			
6.00			3.00	2.00										
Number of Turns	25MS8	25MS9	25MS10	32MS1	32MS2	32MS3	32MS4	32MS5	32MS6	32MS7	40MS1	40MS2		
2.00														
2.25				10.20										
2.50														
3.00	4.00	5.00	6.50		6.8/10.2	7.6/11.7	8.00	6.00	4.00				10.00	
3.50								4.00	2.00	5.00	10.2/11.7			
4.00		3.00								3.00				
4.50														
5.00	2.00		5.00											
5.50						5.0/9.0								
6.00				6.00	4.0/7.0		5.00							
6.50														
7.00											7.0/8.0	7.00		

FIG2		
IFS	Rev01	09/24
ATEX	Rev03	03/24
IECEX	Rev04	03/24
UKEX	Rev01	03/24